

Specification Sheet

Part Number: 181-92003



Wiring Duct Cover for 2" Duct, 6 ft Long, PVC, Intrinsic Blue, 120 ft/carton

Article Number	181-92003
Type	TC2
Color	Blue (BU)
Features & Benefits	<ul style="list-style-type: none">• A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.• Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.• Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)
Quantity Per	carton

Product Description

HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

Short Description	Wiring Duct Cover for 2" Duct, 6 ft Long, PVC, Intrinsic Blue, 120 ft/carton
Global Part Name	TC2-PVC-BU
Technical Description	Wiring Duct Cover for 2" Duct, Intrinsic Blue
Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	2.0
Width W (Metric)	50.8
Height H (Imperial)	0.308
Height H (Metric)	7.82
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	Self-Extinguishing
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)
Reach Complaint(Article 33)	No

ROHS Complaint	Yes
Certification/Specification WEB	EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013 CSA
UL Recognized (US)	Yes
Package Quantity(Imperial)	120
Package Quantity (Metric)	36.58
Customs Number	3925900000