

Specification Sheet

Part Number: 181-92005



Wiring Duct Cover for 2" Duct, 6 ft Long, PVC, Gray, 120 ft/carton

Article Number

181-92005

Type

TC2

Color

Gray (GY)

Features & Benefits

- A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.
 - Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.
 - Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off.
- (Covers to be purchased separately)

Quantity Per

carton

Product Description

HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

Short Description	Wiring Duct Cover for 2" Duct, 6 ft Long, PVC, Gray, 120 ft/carton
Global Part Name	TC2-PVC-GY
Technical Description	Wiring Duct Cover for 2" Duct, Gray
Length L (Imperial)	6.0
Length L (Metric)	1.83
Width W (Imperial)	2.0
Width W (Metric)	50.8
Height H (Imperial)	0.308
Height H (Metric)	7.82
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	Self-Extinguishing
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)
Reach Complaint(Article 33)	No

ROHS Complaint	Yes
Certification/Specification WEB	EN 50085-1:2005 + A1:2013 CSA EN 50085-2-3_1A UL
UL Recognized (US)	Yes
Package Quantity(Imperial)	120
Package Quantity (Metric)	36.58
Customs Number	3925900000