

## Specification Sheet

Part Number: 181-93010



Wiring Duct Cover for 3" Duct, 6 ft Long, PVC, White, 30ft/box

**Article Number**

181-93010

**Type**

TC3

**Color**

White (WH)

**Features & Benefits**

- A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.
  - Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.
  - Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off.
- (Covers to be purchased separately)

**Quantity Per**

box

**Product Description**

HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

<b>Short Description</b>	Wiring Duct Cover for 3" Duct, 6 ft Long, PVC, White, 30ft/box
<b>Global Part Name</b>	TC3-PVC-WH
<b>Technical Description</b>	Wiring Duct Cover for 3" Duct, White
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Width W (Imperial)</b>	3.0
<b>Width W (Metric)</b>	76.2
<b>Height H (Imperial)</b>	0.308
<b>Height H (Metric)</b>	7.82
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-Extinguishing
<b>Halogen free</b>	No
<b>Operating Temperature (Metric)</b>	+122°F (+50°C)
<b>Reach Complaint(Article 33)</b>	No

<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	EN 50085-1:2005 + A1:2013 UL CSA EN 50085-2-3_1A
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	30
<b>Package Quantity (Metric)</b>	9.14
<b>Customs Number</b>	3925900000