

## Specification Sheet

Part Number: 184-11005



High Density Slotted Wall Wiring Duct, 1" x 1", Non-Adhesive, PVC, White, 30ft/Box

**Article Number**

184-11005

**Type**

SLHD1X1

**Color**

White (WH)

**Features & Benefits**

- Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.
- Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.
- Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.
- Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

**Quantity Per**

box

**Product Description**

Pro-Duct high density slotted wall wiring duct features narrow fingers, equaling a 2-to-1 finger ratio compared to standard slotted wall wiring duct. Narrow fingers more readily accommodate compact designs and components.

**Short Description**

High Density Slotted Wall Wiring Duct, 1" x 1", Non-Adhesive, PVC, White, 30ft/Box

**Global Part Name**

SLHD1X1-PVC-WH

**Technical Description**

Non-Adhesive

**Length L (Imperial)**

6.0

**Length L (Metric)**

1.83

**Width W (Imperial)**

1.0

**Width W (Metric)**

25.4

**Height H (Imperial)**

1.06

**Height H (Metric)**

26.9

**Mounting Hole Centers (Imperial)**

2.0

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

Self-Extinguishing

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

EN 50085-2-3\_1A CSA EN 50085-1:2005 + A1:2013 UL

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

30

**Package Quantity (Metric)**

9.14

**Customs Number**

3925900000