

## Specification Sheet

Part Number: 184-21001



High Density Slotted Wall Wiring Duct, 2" x 1", Adhesive, PVC, Gray, 30ft/Box

Article Number	184-21001
Type	SLHDA2X1
Color	Gray (GY)
Features & Benefits	<ul style="list-style-type: none"><li>•Narrow fingers reduce fanning of wires to terminal blocks, providing a neater appearance.</li><li>•Each finger features a double restriction to hold wires in the bottom portion of the duct, simplifying installation.</li><li>•Mounting holes are uniform in size to those in slotted and solid wall duct but are provided every two inches to accommodate compact designs and provide ease of installation.</li><li>•Nonpermanent adhesive allows repositioning prior to final installation.</li></ul>
Quantity Per	box

### Product Description

HellermannTyton High Density Slotted Wall Duct features narrow breakaway fingers, designed at a 2-to-1 ratio compared to standard slotted duct, providing additional access for wire leads. Narrower fingers better accommodate compact designs and components. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

<b>Short Description</b>	High Density Slotted Wall Wiring Duct, 2" x 1", Adhesive, PVC, Gray, 30ft/Box
<b>Global Part Name</b>	SLHDA2X1-PVC-GY
<b>Technical Description</b>	Adhesive
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Width W (Imperial)</b>	2.0
<b>Width W (Metric)</b>	50.8
<b>Height H (Imperial)</b>	1.06
<b>Height H (Metric)</b>	26.9
<b>Mounting Hole Centers (Imperial)</b>	2.0
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-Extinguishing
<b>Halogen free</b>	No
<b>Operating Temperature (Metric)</b>	+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL EN 50085-2-3\_1A CSA EN 50085-1:2005 + A1:2013

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

30

**Package Quantity (Metric)**

9.14

**Customs Number**

3925900000