

Specification Sheet

Part Number: 184-24007



High Density Slotted Wall Wiring Duct, 2" x 4", Non-Adhesive, PVC, White, 120ft/Carton

Article Number	184-24007
Type	SLHD2X4
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">•Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.•Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.•Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.•Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.
Quantity Per	carton

Product Description

HellermannTyton Pro-Duct High-Density, Slotted-Wall Wiring Duct features narrow fingers equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

Short Description

High Density Slotted Wall Wiring Duct, 2" x 4", Non-Adhesive, PVC, White, 120ft/Carton

Global Part Name

SLHD2X4-PVC-WH

Technical Description

Non-Adhesive

Length L (Imperial)

6.0

Length L (Metric)

1.83

Width W (Imperial)

2.0

Width W (Metric)

50.8

Height H (Imperial)

4.07

Height H (Metric)

103.4

Mounting Hole Centers (Imperial)

2.0

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

Self-Extinguishing

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

CSA EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013

UL Recognized (US)

Yes

Package Quantity(Imperial)

120

Package Quantity (Metric)

36.58

Customs Number

3925900000