

## Specification Sheet

Part Number: 184-32003



High Density Slotted Wall Wiring Duct, 3" x 2", Non-Adhesive, PVC, White, 30ft/Box

**Article Number**

184-32003

**Type**

SLHD3X2

**Color**

White (WH)

**Features & Benefits**

- Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.
- Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.
- Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.
- Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

**Quantity Per**

box

**Product Description**

HellermannTyton Pro-Duct High-Density, Slotted-Wall Wiring Duct features narrow fingers equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

<b>Short Description</b>	High Density Slotted Wall Wiring Duct, 3" x 2", Non-Adhesive, PVC, White, 30ft/Box
<b>Global Part Name</b>	SLHD3X2-PVC-WH
<b>Technical Description</b>	Non-Adhesive
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Width W (Imperial)</b>	3.0
<b>Width W (Metric)</b>	76.2
<b>Height H (Imperial)</b>	2.07
<b>Height H (Metric)</b>	52.6
<b>Mounting Hole Centers (Imperial)</b>	2.0
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-Extinguishing
<b>Halogen free</b>	No
<b>Operating Temperature (Metric)</b>	+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL CSA EN 50085-2-3\_1A EN 50085-1:2005 + A1:2013

**UL Recognized (US)**

Yes

**Package Quantity(Imperial)**

30

**Package Quantity (Metric)**

9.14

**Customs Number**

3925900000