

Specification Sheet

Part Number: 184-43002



High Density Slotted Wall Wiring Duct, 4" x 3", Non-Adhesive, PVC, White, 30ft/Box

Article Number

184-43002

Type

SLHD4X3

Color

White (WH)

Features & Benefits

- Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.
- Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.
- Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.
- Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

Quantity Per

box

Product Description

HellermannTyton Pro-Duct High-Density, Slotted-Wall Wiring Duct features narrow fingers equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

Short Description

High Density Slotted Wall Wiring Duct, 4" x 3", Non-Adhesive, PVC, White, 30ft/Box

Global Part Name

SLHD4X3-PVC-WH

Technical Description

Non-Adhesive

Length L (Imperial)

6.0

Length L (Metric)

1.83

Width W (Imperial)

4.0

Width W (Metric)

101.6

Height H (Imperial)

3.07

Height H (Metric)

77.9

Mounting Hole Centers (Imperial)

2.0

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

Self-Extinguishing

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

CSA EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013

UL Recognized (US)

Yes

Package Quantity(Imperial)

30

Package Quantity (Metric)

9.14

Customs Number

3925900000