

Specification Sheet

Part Number: SNP3210K2



Article Number

190-00142

Type

SNP32

Color

White (WH)

Features & Benefits

- Designed for quick, ratcheted installation and can be released and reused.
- Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

Quantity Per

bag

Product Description

Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments. A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends. Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases. The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.

Short Description

Snapper Hose Clamp, 1.21"-1.38" Bundle Diameter, POM, White, 50/pkg

Global Part Name

SNP32-POM-WH

Fixation Method

Plug-in mounting

Variant

Closed

Bundle Diameter Min (Imperial)

1.2

Bundle Diameter Min (Metric)

31.0

Bundle Diameter Max (Imperial)

1.4

Bundle Diameter Max (Metric)

35.5

Wall Thickness WT (Imperial)

.068

Wall Thickness WT (Metric)

1.7

Material	Polyacetal (POM)
Material Shortcut	POM
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988