

Specification Sheet

Part Number: SNP810C2



Snapper Hose Clamp, .51"—.59" Bundle Diameter, POM, White, 100/pkg

Article Number	190-00224
Type	SNP8
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• Designed for quick, ratcheted installation and can be released and reused.• Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.
Quantity Per	bag

Product Description

Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments. A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends. Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases. The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.

Short Description

Snapper Hose Clamp, .51"-.59" Bundle Diameter, POM, White, 100/pkg

Global Part Name

SNP8-POM-WH

Fixation Method

Plug-in mounting

Variant

Closed

Wall Thickness WT (Imperial)

.069

Wall Thickness WT (Metric)

1.8

Material

Polyacetal (POM)

Material Shortcut

POM

Flammability

UL 94 HB

UV Resistant (Yes/No)

No

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988