

Specification Sheet

Part Number: SNP90GHS0X2



Article Number

190-00232

Type

SNP90

Color

Black (BK)

Features & Benefits

- Designed for quick, ratcheted installation and can be released and reused. • Heat stabilized material is suitable for high temperature applications.

Quantity Per

bag

Product Description

Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments. A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends. Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases. The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.

Short Description

Snapper Hose Clamp, 3.46"-3.82" Bundle Diameter, PA66GF13, Black, 25/pkg

Global Part Name

SNP90-PA66GF13-BK

Fixation Method

Plug-in mounting

Variant

Closed

Bundle Diameter Min (Imperial)

3.48

Bundle Diameter Min (Metric)

88.5

Bundle Diameter Max (Imperial)

3.9

Bundle Diameter Max (Metric)

98

Wall Thickness WT (Imperial)

.098

Wall Thickness WT (Metric)

2.4

Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
Material Shortcut	PA66GF13
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988