

Specification Sheet

Part Number: PHSNP38-100



Article Number

191-00012

Type

PHSNP38-100

Color

Metal (ML)

Features & Benefits

Designed to ease and speed up the application of snapper on production assembly lines.

Quantity Per

box

Product Description

Snapper installation tools are available in both pneumatic and mechanical version. They are specifically developed to increase reliability, reduce operator fatigue and installation time.

Short Description

Pneumatic Snapper Hose Clamp Tool for Snappers 38-100

Global Part Name

PHSNP38-100-MET-ML

Material	Metal (MET)
Material Shortcut	MET
ROHS Complaint	Yes
Package Quantity(Imperial)	1
Package Quantity (Metric)	1
Customs Number	8467195090
Weight (Metric)	2.27
Weight (Imperial)	5.0