

## Specification Sheet

Part Number: 211-00265



P-Clamp, 0.39" Wide, 0.31" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66, Natural, 100/pkg

<b>Article Number</b>	211-00265
<b>Type</b>	H4P
<b>Color</b>	Natural (NA)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• P-Clamps easily guide and locate wire and cables up to 1" in diameter.</li><li>• Designed with a radius edge to prevent chafing and cutting into insulation.</li></ul>
<b>Quantity Per</b>	EA
<b>Product Description</b>	HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.
<b>Short Description</b>	P-Clamp, 0.39" Wide, 0.31" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66, Natural, 100/pkg

Global Part Name

H4P-PA66-NA

Fixation Method

screw-hole

Variant

Closed

Width W (Imperial)

0.39

Width W (Metric)

10.0

Bundle Diameter Max (Imperial)

0.31

Bundle Diameter Max (Metric)

8.0

Nominal Diameter (Imperial)

5/16

Nominal Diameter (Metric)

8.0

Wall Thickness WT (Imperial)

0.047

Wall Thickness WT (Metric)

1.2

Mounting Hole Diameter D (Imperial)

0.17

Mounting Hole Diameter D (Metric)

4.2 mm

Mounting Hole Diameter D Min (Imperial)

0.17

Mounting Hole Diameter D Max (Imperial)

0.17

Mounting Hole Diameter D Max (Metric)

4.2

Mounting Hole Centers (Imperial)

0.39

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>UV Resistant (Yes/No)</b>	No
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988