

Specification Sheet

Part Number: 211-60010



P-Clamp, 0.39" Wide, 0.13" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS, Black, 1000/pkg

Article Number	211-60010
Type	H1P
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• P-Clamps easily guide and locate wire and cables up to 1" in diameter.• Designed with a radius edge to prevent chafing and cutting into insulation.
Quantity Per	bag
Product Description	HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.
Short Description	P-Clamp, 0.39" Wide, 0.13" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS, Black, 1000/pkg

Global Part Name

H1P-PA66HS-BK

Fixation Method

screw-hole

Variant

Closed

Width W (Imperial)

0.39

Width W (Metric)

10.0

Bundle Diameter Max (Imperial)

0.13

Bundle Diameter Max (Metric)

3.2

Nominal Diameter (Imperial)

1/8

Nominal Diameter (Metric)

3.2

Wall Thickness WT (Imperial)

0.031

Wall Thickness WT (Metric)

0.8

Mounting Hole Diameter D (Imperial)

0.17

Mounting Hole Diameter D (Metric)

4.2 mm

Mounting Hole Diameter D Min (Imperial)

0.17

Mounting Hole Diameter D Max (Imperial)

0.17

Mounting Hole Diameter D Max (Metric)

4.2

Mounting Hole Centers (Imperial)

0.33

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
UV Resistant (Yes/No)	No
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	0.3

