

Specification Sheet

Part Number: MCRFW-BS



InfoStream Multi-Channel Raceway Base Splice, PVC, Office White, 10/pkg

Article Number

250-00004

Type

MCR-BS

Color

Office White (OEWH)

Features & Benefits

- Raceway and fittings are manufactured from a UL 94V-0 rated material to insure compliance with codes
- All fittings have been designed to maintain the required 1" minimum bend radius to meet TIA/EIA-568-B and 569-A standard
- Raceway and fittings are U.L. Listed to 600 Volts to meets new UL5A and CSA 22.2 No. 62-93 standards
- Patented hinged cover speeds installation time by allowing installer to partially mount cover prior to laying cables

Quantity Per

bag

Product Description

HellermannTyton's InfoStream non-metallic raceway system can accommodate up to four separate channels of electrical, voice, data, video or fiber optic cabling. The elliptical shape is aesthetically pleasing when compared to other designs. The raceway's unique and patented design make installations quicker and easier.

Short Description	InfoStream Multi-Channel Raceway Base Splice, PVC, Office White, 10/pkg
Global Part Name	MCR-BS-PVC-WH
Width W (Imperial)	4.5
Width W (Metric)	114.3
Height H (Imperial)	2.05
Height H (Metric)	52.07
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V0
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)
Reach Complaint(Article 33)	No
ROHS Complaint	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes

Package Quantity(Imperial)

10

Package Quantity (Metric)

10

Customs Number

3925900000