

## Specification Sheet

Part Number: MCRI-CD10



InfoStream Multi-Channel Raceway Center Divider, 10 ft Long, PVC, Ivory, 120ft/pkg

<b>Article Number</b>	250-00038
<b>Type</b>	MCR-CD10
<b>Color</b>	Ivory (IV)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Raceway and fittings are manufactured from a UL94 V0 rated material to insure compliance with codes.</li><li>•All fittings have been designed to maintain the required 1" minimum bend radius to meet TIA/EIA-568-B and 569-A standard.</li><li>•Raceway and fittings are UL Listed to 600 Volts to meet new UL5A and CSA 22.2 No. 62-93 standards.</li></ul>
<b>Quantity Per</b>	box
<b>Product Description</b>	HellermannTyton's InfoStream non-metallic raceway system can accommodate up to four separate channels of electrical, voice, data, video or fiber optic cabling. The elliptical shape is aesthetically pleasing when compared to other designs. The raceway's unique and patented design make installations quicker and easier.

**Short Description**

InfoStream Multi-Channel Raceway Center Divider, 10 ft Long, PVC, Ivory, 120ft/pkg

**Global Part Name**

MCR-CD10-PVC-BGE

**Length L (Imperial)**

10.0

**Length L (Metric)**

3.04

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

UL 94 V0

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

120

**Package Quantity (Metric)**

36.58

**Customs Number**

3925900000

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)