

## Specification Sheet

Part Number: TSR1FW-12



Reducer, 1-3/4" to 1-1/4" (TSR3 to TSR2), PVC, Office White, 1/bag

**Article Number**

250-01120

**Type**

TSR1-12

**Color**

Office White (OEWH)

**Features & Benefits**

- Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.
- PVC construction is lightweight, durable and more affordable than metallic raceway systems.
- Flexible hinge is designed to reduce stress cracking and discoloration from repeated opening and closing.
- Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.
- Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.

**Quantity Per**

bag

**Product Description**

HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSR surface raceway systems can be used to route a variety of communication cable, including high speed UTP and fiber optic cable.

**Short Description**

Reducer, 1-3/4" to 1-1/4" (TSR3 to TSR2), PVC, Office White, 1/bag

**Global Part Name**

TSR1-12-PVC-WH

**Material**

Polyvinylchloride (PVC)

**Material Shortcut**

PVC

**Flammability**

UL 94 V0

**Halogen free**

No

**Operating Temperature (Metric)**

+122°F (+50°C)

**Reach Complaint(Article 33)**

No

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)**

1

**Customs Number**

3925900000

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)