

Specification Sheet

Part Number: TSR3I-33-1



Internal Corner Cover, 1-3/4", 1" Bend Radius, PVC, Ivory, 1/bag

Article Number

250-03334

Type

TSR3-33-1

Color

Ivory (IV)

Features & Benefits

- Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.
- PVC construction is lightweight, durable and more affordable than metallic raceway systems.
- Flexible hinge is designed to reduce stress cracking and discoloration from repeated opening and closing.
- Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.
- Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.

Quantity Per

bag

Product Description

HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSR surface raceway systems can be used to route a variety of communication cable, including high speed UTP and fiber optic cable.

Short Description

Internal Corner Cover, 1-3/4", 1" Bend Radius, PVC, Ivory, 1/bag

Global Part Name

TSR3-33-1-PVC-BGE

Width W (Imperial)

1.75

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

UL 94 V0

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

3925900000