

Specification Sheet

Part Number: TSR3I-6A



One Piece Surface Raceway, 1-3/4", 6.0 ft Long, PVC, Ivory, 120ft/Carton

Article Number	250-03601
Type	TSR3-6A
Color	Ivory (IV)
Features & Benefits	<ul style="list-style-type: none">• Tamper resistant, self-locking hidden positive latch permits quick re-entry as well as providing a secure installation of premise wire.• Fittings incorporate a minimum 1" bend radius per ANSI/TIA-568-C and 569-A standards.• Rubber-based, foam-tape adhesive with high ultimate bond strength conforms to any surface.• Flexible hinge allows the raceway to endure numerous openings without creating discoloration or stress cracking
Quantity Per	carton

Product Description

HellermannTyton's low voltage raceway (TSR) is a one piece, non-metallic, adhesive backed, latching raceway designed to aesthetically organize and route communications wires, including high speed UTP cable and fiber optic cable, from the telecom room to the work area.

Short Description

One Piece Surface Raceway, 1-3/4", 6.0 ft Long, PVC, Ivory, 120ft/Carton

Global Part Name

TSR3-6A-PVC-BGE

Length L (Imperial)

6.0

Length L (Metric)

1.83

Width W (Imperial)

1.75

Width W (Metric)

44.45

Height H (Imperial)

1.0

Height H (Metric)

25.40

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

UL 94 V0

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Package Quantity(Imperial)

120

Package Quantity (Metric)

36.58

Customs Number

3925900000