

Specification Sheet

Part Number: FPC



Grommet, Panel Thickness 0.083"-0.130", PE, Natural, 82ft/pkg

Article Number

251-10309

Type

G51PC

Color

Natural (NA)

Features & Benefits

- Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.
- Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

Quantity Per

reel

Product Description

HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

Short Description

Grommet, Panel Thickness 0.083"-0.130", PE, Natural, 82ft/pkg

Global Part Name

G51PC-PE-NA

Length L (Imperial)

82.0

Variant

Open

Width W (Imperial)

0.224

Width W (Metric)

5.7

Height H (Imperial)

0.169

Height H (Metric)

4.3

Panel Thickness Min(Imperial)

0.083

Panel Thickness Max(Imperial)

0.13

Panel Thickness Min (Metric)

2.10

Panel Thickness Max (Metric)

3.30

Material

Polyethylene (PE)

Material Shortcut

PE

Flammability

UL 94 HB

Halogen free

Yes

Operating Temperature (Metric)	-22°F to +176°F (-30°C to +80°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	82
Package Quantity (Metric)	25
Customs Number	3926909988
Content Unit(BMEcat)	reel
Weight (Metric)	0.38