


## Specification Sheet

Part Number: FPH



Grommet, Panel Thickness 0.382"-0.508", PE, Natural, 82ft/pkg

<b>Article Number</b>	251-10809
<b>Type</b>	G51PH
<b>Color</b>	Natural (NA)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.</li><li>• Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.</li></ul>
<b>Quantity Per</b>	reel
<b>Product Description</b>	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
<b>Short Description</b>	Grommet, Panel Thickness 0.382"-0.508", PE, Natural, 82ft/pkg

**Global Part Name**

G51PH-PE-NA

**Length L (Imperial)**

82.0

**Variant**

Open

**Width W (Imperial)**

0.646

**Width W (Metric)**

16.4

**Height H (Imperial)**

0.268

**Height H (Metric)**

6.8

**Panel Thickness Min(Imperial)**

0.382

**Panel Thickness Max(Imperial)**

0.508

**Panel Thickness Min (Metric)**

9.70

**Panel Thickness Max (Metric)**

12.90

**Material**

Polyethylene (PE)

**Material Shortcut**

PE

**Flammability**

UL 94 HB

**Halogen free**

Yes

<b>Operating Temperature (Metric)</b>	-22°F to +176°F (-30°C to +80°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	82
<b>Package Quantity (Metric)</b>	25
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	reel
<b>Weight (Metric)</b>	1.15