

Specification Sheet

Part Number: 309-65139



Article Number	309-65139
Type	TFN21-ST 4.8/2.4
Color	Yellow (YE)
Features & Benefits	<ul style="list-style-type: none">• Thin, 2 to 1 shrink ratio tubing provides insulation and abrasion protection for wires and cables.• Flammability rating of UL224 VW-1 for use in applications requiring the highest degree of flame protection (excludes clear tubing).• Flexible-yet-durable material resists most common oils, chemicals and fluids.• Available in a variety of diameters and colors for identifying and marking wires and cables.• Available in mini reels, bulk reels, and sticks for small to large volume applications.
Quantity Per	pack
Product Description	TFN21 is a highly flexible thin wall heat shrink tubing with a 2 to 1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. Available in mini reels, bulk reels and sticks, for small to large volume applications.

Short Description	Heat Shrink Tubing, 4' Long Stick, 2:1 Shrink Ratio, 3/16", 4.8/2.4 Dia, PO, Yellow, 20/pkg
Global Part Name	TFN21-ST 4.8/2.4-PO-X-YE
Variant	Thin-Wall
Nominal Diameter (Imperial)	3/16
Nominal Diameter (Metric)	4.8
Wall Thickness WT (Imperial)	.019
Wall Thickness WT (Metric)	0.48
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Flammability	UL 224 VW-1
Halogen free	No
Operating Temperature (Metric)	-67°F to +275°F (-55°C to +135°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL ANSI/UL 224

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

20

Package Quantity (Metric)

20

Customs Number

3926909987