

Specification Sheet

Part Number: 318-60155



Heat Shrink Tubing, 4' Long Stick, Adhesive Lined, 3:1 Shrink Ratio, 3/4", 19.0/6.0 Dia, PO, Black, 15/pkg

Article Number	318-60155
Type	TAN33-ST-19/6 BK
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Adhesive lining provides an excellent seal against moisture and humidity.• Thin exterior wall is very flexible, while providing superior insulation of cables and components.• 3 to 1 shrink ratio accommodates a wide range of component shapes and diameters.• Meets UL224 VW-1 specifications, making it ideal for high heat applications (excludes clear tubing).• Polyolefin material provides mechanical strength with good resistance to solvents, oils and fuels.• 4-foot sticks are individually tagged and come in a retail box.
Quantity Per	pack

Product Description

TAN33 is a flexible, thin wall adhesive-lined heat shrink tubing with highly flame retardant properties. The 3 to 1 shrink ratio accommodates a wide range of component shapes and diameters. The adhesive lining begins to activate as the temperature reaches 176° F (80° C), to create a strong seal against moisture and humidity.

Short Description

Heat Shrink Tubing, 4' Long Stick, Adhesive Lined, 3:1 Shrink Ratio, 3/4", 19.0/6.0 Dia, PO, Black, 15/pkg

Global Part Name

TAN33-ST-19/6 BK-PO-X-BK

Length L (Imperial)

4.0

Length L (Metric)

1.22

Variant

Thin-Wall

Nominal Diameter (Imperial)

3/4

Nominal Diameter (Metric)

19

Wall Thickness WT (Imperial)

.085

Wall Thickness WT (Metric)

2.15

Material

Polyolefin, cross-linked (PO-X)

Material Shortcut

PO-X

Adhesive

Hot melt adhesive

Halogen free No

Operating Temperature (Metric) -67°F to +257°F (-55°C to +125°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial) 15

Package Quantity (Metric) 15

Customs Number 3926909987