

Specification Sheet

Part Number: 323-50010



Heat Shrink Tubing, 4' Long Stick, Medium Wall Adhesive Lined, Up to 4:1, 1/2", 12/3 dia, PO, Black, 6/pkg

Article Number	323-50010
Type	TREDUX MA47-48ST-12/3
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Medium wall tubing resists solvents, acids and alkaline solutions while providing good mechanical strength.• Features robust insulation characteristics designed for low voltage power applications.• Adhesive lining provides excellent insulation against moisture and humidity.• RoHS compliant and Halogen-free.
Quantity Per	pcs.

Product Description

MA47 is a medium wall heat shrink tubing with an adhesive lining for use in low voltage applications. The thermoplastic adhesive liner provides excellent moisture sealing and insulation protection of cable joints and terminations. Made of a polyolefin outer material, this tubing has a shrink ratio up to 4 to 1. The adhesive lining begins to activate as the temperature approaches 185° F (85° C). Individually labeled 4-foot sticks come packaged in a retail display box.

Short Description

Heat Shrink Tubing, 4' Long Stick, Medium Wall Adhesive Lined, Up to 4:1, 1/2", 12/3 dia, PO, Black, 6/pkg

Global Part Name

TREDUX MA47-48ST-12/3-PO-X-BK

Length L (Imperial)

4.0

Length L (Metric)

1.0

Voltage Range

Low and medium voltage

Variant

Medium-Wall

Nominal Diameter (Imperial)

1/2

Nominal Diameter (Metric)

12

Wall Thickness WT (Imperial)

.08

Wall Thickness WT (Metric)

2.0

Material

Polyolefin, cross-linked (PO-X)

Material Shortcut

PO-X

Adhesive	Hot melt adhesive
Flammability	Not Flame Retardant
Halogen free	Yes
Operating Temperature (Metric)	-67°F to +230°F (-55°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	6
Package Quantity (Metric)	6
Customs Number	3926909987
Weight (Metric)	0.39
Weight (Imperial)	0.85