

Specification Sheet

Part Number: 544-80102



M-Boss Marker, 3.54" Wide x 0.39" High, Stainless Steel, Silver, 500/Box

Article Number	544-80102
Type	MBML10X90
Color	Metal (ML)
Features & Benefits	<ul style="list-style-type: none">• Raised marking ensure text visibility even when covered in dust, debris, grease and oil.• Stainless steel grade SS316 is suited for use in harsh environments.• Marker plates are designed for use with stainless steel cable ties with a 0.81" (4.6mm) strap width.
Quantity Per	box
Product Description	M-Boss Compact is quiet, easy to use metal plate embossing printer with a small production footprint. It is simple to install and operate only needs a standard electrical supply and a PC. Marker plates are attached to pipes and cables using 4.6mm width MBT cable ties and a MK9SST hand tool.
Short Description	M-Boss Marker, 3.54" Wide x 0.39" High, Stainless Steel, Silver, 500/Box

Global Part Name

MBML10X90-SS316-ML

Technical Description

M-Boss Marker, .39" Wide X 3.54" Long, Silver

Length L (Metric)

89.5

Fixation Method

Others

Variant

Other

Width W (Imperial)

3.54

Width W (Metric)

10.0

Height H (Imperial)

0.39

Height H (Metric)

9.91

Diameter D (imperial)

0.236

Diameter D (metric)

6

Cable Tie Width Max (Imperial)

0.18

Cable Tie Width Max (Metric)

4.6

Bolt Size

MBT Metal ties max width 4.6 mm

Material

Stainless Steel (SS316)

Material Shortcut SS316

Halogen free Yes

Operating Temperature (Metric) -112°F to +1000°F (-80°C to +538°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Package Quantity(Imperial) 500

Package Quantity (Metric) 500

Customs Number 7326908695

Content Unit(BMEcat) pcs.

Weight (Metric) 1.161

Weight (Imperial) 2.559