

Specification Sheet

Part Number: 553-50020



ShrinkTrak Labels, 1-Sided, Unslit, .25" (6.35mm), PO-X, Yellow, 250/box

| | |
|---------------------|---|
| Article Number | 553-50020 |
| Type | HST6-2YE |
| Color | Yellow (YE) |
| Features & Benefits | <ul style="list-style-type: none">• Slide Slit and optional center slits for easy wire insertion.• Smooth surface for clean and legible printing.• Supplied on a ladder style carrier so that markers can be kitted after printing.• A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters. |
| Quantity Per | box |

Product Description

HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

| | |
|---------------------------------------|--|
| Short Description | ShrinkTrak Labels, 1-Sided, Unslit, .25" (6.35mm), PO-X, Yellow, 250/box |
| Global Part Name | HST6-2YE-PO-X-YE |
| Variant | Thin-Wall |
| Width W (Imperial) | 1.9 |
| Width W (Metric) | 48.26 |
| Thickness T (Imperial) | .003 |
| Thickness T (Metric) | .0762 |
| Height H (Imperial) | 0.42 |
| Height H (Metric) | 10.67 |
| Width of Liner (Metric) | 76.2 |
| Width of Liner (imperial) | 3.0 |
| Outside Diameter OD(Imperial) | 0.25 |
| Outside Diameter OD(metric) | 6.35 |
| Outside Diameter Max(Imperial) | 0.25 |
| Outside Diameter Max (metric) | 6.35 |
| Wall Thickness WT (Imperial) | 0.028 |
| Wall Thickness WT (Metric) | 0.71 |

| | |
|-----------------|---------------------------------|
| Material | Polyolefin, cross-linked (PO-X) |
|-----------------|---------------------------------|

Material Shortcut PO-X

| | |
|--------------------|-----------------------------------|
| US MIL SPEC | SAE-AMS-DTL-23053/5 Class 1 and 3 |
|--------------------|-----------------------------------|

SAE-AS81531
MIL-STD-202G Method 215K

Flammability

UL 224 VW-1

Halogen free

No

Operating Temperature (Metric)

-67°F to +275°F (-55°C to +135°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Certification/Specification WEB

SAE - AS81531 SAE - AMS - DTL-23053/5 Class 1 and 3 UL 224 125 °C
600V VW-1

| | |
|-----------------------------------|-----|
| Package Quantity(Imperial) | 250 |
|-----------------------------------|-----|

Package Quantity (Metric) 250

| | |
|-----------------------|------------|
| Customs Number | 3917320000 |
|-----------------------|------------|

Content Unit(BMEcat) pack

| | |
|--------------------------|-------|
| Labels per Column | 1 |
| Labels per Row | 1 |
| Weight (Metric) | 0.362 |
| Weight (Imperial) | 0.79 |