

## Specification Sheet

Part Number: 553-50066



ShrinkTrak Labels, 1-Sided, 4-Slit, .38" (9.52mm), PO-X, White, 1000/box

Article Number	553-50066
Type	HST9-3WH-3S
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none"><li>• Slide Slit and optional center slits for easy wire insertion.</li><li>• Smooth surface for clean and legible printing.</li><li>• Supplied on a ladder style carrier so that markers can be kitted after printing.</li><li>• A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.</li></ul>
Quantity Per	box

### Product Description

HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

<b>Short Description</b>	ShrinkTrak Labels, 1-Sided, 4-Slit, .38" (9.52mm), PO-X, White, 1000/box
<b>Global Part Name</b>	HST9-3WH-3S-PO-X-WH
<b>Variant</b>	Thin-Wall
<b>Width W (Imperial)</b>	0.475
<b>Width W (Metric)</b>	12.07
<b>Thickness T (Imperial)</b>	.003
<b>Thickness T (Metric)</b>	.0762
<b>Height H (Imperial)</b>	0.597
<b>Height H (Metric)</b>	15.16
<b>Width of Liner (Metric)</b>	76.2
<b>Width of Liner (imperial)</b>	3.0
<b>Outside Diameter OD(Imperial)</b>	0.375
<b>Outside Diameter OD(metric)</b>	9.52
<b>Outside Diameter Max(Imperial)</b>	0.375
<b>Outside Diameter Max (metric)</b>	9.52
<b>Wall Thickness WT (Imperial)</b>	0.031
<b>Wall Thickness WT (Metric)</b>	0.79

<b>Material</b>	Polyolefin, cross-linked (PO-X)
-----------------	---------------------------------

**Material Shortcut** PO-X

<b>US MIL SPEC</b>	MIL-STD-202G Method 215K
--------------------	--------------------------

SAE-AS81531

SAE-AMS-DTL-23053/5 Class 1 and 3

**Flammability**

UL 224 VW-1

**Halogen free**

No

**Operating Temperature (Metric)**

-67°F to +275°F (-55°C to +135°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Certification/Specification WEB**

CEN

<b>Package Quantity(Imperial)</b>	1000
-----------------------------------	------

**Package Quantity (Metric)** 1000

<b>Customs Number</b>	3917320000
-----------------------	------------

**Content Unit(BMEcat)** pack

<b>Labels per Column</b>	1
--------------------------	---

**Labels per Row** 4

**Weight (Metric)** 0.43

**Weight (Imperial)** 0.93