

Specification Sheet

Part Number: 553-50084



ShrinkTrak Labels, 1-Sided, 1-Slit, .25" (6.35mm), PO-X, White, 2000/box

Article Number	553-50084
Type	HST6-2WH-S
Color	White (WH)
Features & Benefits	• Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
Quantity Per	box

Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
---------------------	--

Short Description	ShrinkTrak Labels, 1-Sided, 1-Slit, .25" (6.35mm), PO-X, White, 2000/box
Global Part Name	HST6-2WH-S-PO-X-WH
Variant	Thin-Wall
Width W (Imperial)	0.95
Width W (Metric)	24.13
Thickness T (Imperial)	.003
Thickness T (Metric)	.0762
Height H (Imperial)	0.42
Height H (Metric)	10.67
Width of Liner (Metric)	76.2
Width of Liner (imperial)	3.0
Outside Diameter OD(Imperial)	0.25
Outside Diameter OD(metric)	6.35
Outside Diameter Max(Imperial)	0.25
Outside Diameter Max (metric)	6.35
Wall Thickness WT (Imperial)	0.028
Wall Thickness WT (Metric)	0.71

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AMS-DTL-23053/5 Class 1 and 3
MIL-STD-202G Method 215K SAE-AS81531	
Flammability	
UL 224 VW-1	Halogen free
No	Operating Temperature (Metric)
-67°F to +275°F (-55°C to +135°C)	Reach Complaint(Article 33)
Yes	ROHS Complaint
Yes	Certification/Specification WEB
CEN	
Package Quantity(Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3917320000
Content Unit(BMEcat)	pack
Labels per Column	1

Labels per Row

2

Weight (Metric)

0.793

Weight (Imperial)

1.73