

Specification Sheet

Part Number: 558-00330



Article Number

558-00330

Type

HT3OE75250

Color

Orange (OG)

Features & Benefits

- Continuous Colored Signal Panel labels come with yellow or orange stripes for easy printing of caution and warning labels.
- Continuous labels allow for designing and cutting labels to any length.
- Various widths are available so that a wide variety of sign sizes can be customized and produced on demand.

Quantity Per

roll

Product Description

The Pre-printed colored header vinyl rolls can be used to design signs that conform to Occupational Safety and Hazard Association (OSHA) and American National Standards Institute (ANSI) requirements for Warning and Caution Signs and markers. All can be designed, printed and cut to length in Tagprint Pro and any HellermannTyton thermal transfer printing system.

| | |
|----------------------------------|--|
| Short Description | Adhesive Labels, Banded Color Continuous Roll, 3.0" x 250', PET, Orange/White, 250 ft/roll |
| Global Part Name | HT3OE75250-336/926-OG |
| Technical Description | Banded Colored Continuous Roll, 3.0" X 250', Orange/White |
| Length L (Imperial) | 250.0 |
| Length L (Metric) | 76.2 |
| Variant | 3.2mil, 50lb bleached kraft paper |
| Width W (Imperial) | 3.0 |
| Width W (Metric) | 76.2 |
| Thickness T (Metric) | 64.0 |
| Width of Liner (Metric) | 76.2 |
| Width of Liner (imperial) | 3.0 |
| Material | Type 336/926, Polyester (PET), UV stable, clear Polyester laminate |
| Material Shortcut | 336/926 |
| Adhesive | Acrylic |
| Halogen free | No |

| | |
|--|-----------------------------------|
| Adhesive Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
| Operating Temperature (Metric) | -40°F to +302°F (-40°C to +150°C) |
| Reach Complaint(Article 33) | Yes |
| ROHS Complaint | Yes |
| Certification/Specification WEB | UL 969 CSA |
| Package Quantity(Imperial) | 250 |
| Package Quantity (Metric) | 76.20 |
| Customs Number | 3919102055 |
| Labels per Column | 1 |
| Labels per Row | 1 |
| Weight (Metric) | 0.68 |
| Weight (Imperial) | 1.48 |