

Specification Sheet

Part Number: 558-00407



Adhesive Labels, Solid Color Continuous Roll, Reflective, 4.0" x 100', VL, Red, 100 ft/roll

Article Number

558-00407

Type

HT4RDF100

Color

Red Reflective (RDRF)

Features & Benefits

- Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.
- The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.
- Signs can be designed in Tagprint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.

Quantity Per

roll

Product Description

Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.

Short Description

Adhesive Labels, Solid Color Continuous Roll, Reflective, 4.0" x 100', VL, Red, 100 ft/roll

Global Part Name

HT4RDF100-V-RD

Technical Description

Solid Colored Continuous Roll, Reflective, 4.0" X 100', Vinyl, Red

Length L (Imperial)

100.0

Length L (Metric)

30.48

Variant

3.2mil, 50lb bleached kraft paper

Width W (Imperial)

4.0

Width W (Metric)

101.6

Width of Liner (Metric)

101.6

Width of Liner (imperial)

4.0

Material

Vinyl

Material Shortcut

V

Adhesive	Acrylic
Halogen free	No
UV Resistant (Yes/No)	Yes
Adhesive Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Operating Temperature (Metric)	-40°F to +180°F (-40°C to +82°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL 969
Package Quantity(Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3919102055
Labels per Column	1
Labels per Row	1
Weight (Metric)	2.04
Weight (Imperial)	4.50

