

Specification Sheet

Part Number: 558-00503



Adhesive Labels, Solid Color Continuous Roll, Reflective, 3.0" x 100', UV Stable PET, Red, 100 ft/roll

Article Number	558-00503
Type	HT3RDHB250
Color	Red (RD)
Features & Benefits	<ul style="list-style-type: none">• Continuous Polyester Labels are made with UV stable materials for long outdoor life.• Labels use UV stable permanent ink.• Continuous polyester is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.
Quantity Per	roll

Product Description

Continuous Polyester Labels are made with UV stable materials for long outdoor life. The labels are made with UV stable permanent inks for long term fade resistance. The Continuous Polyester is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

Short Description	Adhesive Labels, Solid Color Continuous Roll, Reflective, 3.0" x 100', UV Stable PET, Red, 100 ft/roll
Global Part Name	HT3RDHB250-840/926-RD
Technical Description	Solid Colored Continuous Roll, Reflective, 3.0" X 100', Red
Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	3.0
Width W (Metric)	76.2
Width of Liner (Metric)	76.2
Width of Liner (imperial)	3.0
Material	Type 840/926, Polyester (PET), UV stable, clear Polyester laminate
Material Shortcut	840/926
Adhesive	Acrylic
Halogen free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)

Operating Temperature (Metric) -40°F to +302°F (-40°C to +150°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB IFC 2012 UL 969 CSA 66956 NEC2011 NEC2014 ANSI Standard Z535.4

UL Recognized (US) Yes

Package Quantity(Imperial) 100

Package Quantity (Metric) 30.48

Customs Number 3919102055

Labels per Column 1

Labels per Row 1

Weight (Metric) 0.544

Weight (Imperial) 1.199