

Specification Sheet

Part Number: 591-00244



Spirit Printer Refill Labels, 1.0" x 30', VL, White, 1/pkg

Article Number	591-00244
Type	SP1WH30
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• The Spirit printer is portable which allows the user to design and print signs and pipe markers remotely.• Almost unlimited design and printed label formats can be made because the Spirit uses a colored continuous vinyl in a variety of colors from .5" (12.7mm) to 2.0" (50.8mm) wide.• The printer has a built in cutter that cuts the vinyl to length when printed.• Many colored ribbon inks allow designs that incorporate a variety of vinyl and ink colors to meet any code or visibility requirements.
Quantity Per	roll

Product Description

The Spirit printer allows the user to design and print signs and pipe markers remotely using continuous adhesive vinyl tapes that come in a variety of colors from .5" (12.7mm) to 2.0" (50.8mm) wide. The printer has a built in cutter that cuts the vinyl to length when printed. Many colored ribbon inks allow designs that incorporate a variety of vinyl and ink colors to meet any code or visibility requirements.

Short Description	Spirit Printer Refill Labels, 1.0" x 30', VL, White, 1/pkg
Global Part Name	SP1WH30-V-WH
Technical Description	Sport Printer Refill Label Roll, 1.0" X 30', White
Length L (Imperial)	1.0
Length L (Metric)	25.4
Fixation Method	Pasting / Stick
Variant	Roller form
Width W (Imperial)	1.0
Width W (Metric)	25.4
Height H (Imperial)	1.0
Height H (Metric)	25.40
Width of Liner (Metric)	25.4
Width of Liner (imperial)	1.0
Material	Vinyl
Material Shortcut	V

Operating Temperature (Metric)

-40°F to +180°F (-40°C to +82°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

30

Package Quantity (Metric)

9.14

Customs Number

3919102055