

Specification Sheet

Part Number: TAG26J-994



Article Number

593-26994

Type

TAG26J

Color

White (WH)

Features & Benefits

- HellermannTyton Ink Jet labels are sheet fed for easy loading and fast printing.
- Ink Jet labels are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing.
- Ink Jet labels are printable using toner for long term UV exposure.
- Ink Jet labels come in a variety of label sizes and types to fit most applications.

Quantity Per

pack

Product Description

HellermannTyton's ink jet self-laminating labels are smear resistant, allowing them to be handled immediately. The labels are made of a heat resistant 1mm polyester film with a strong acrylic based adhesive. The printable area is a special ink-receptive film that absorbs the ink as it is printed on an ink jet printer.

Short Description

Ink Jet Label, Self-Laminating, .50" x .35" x .75", 128 Per Sheet, PET, White, 2500/pkg

Global Part Name

TAG26J-994-WH

Width W (Imperial)

0.5

Width W (Metric)

12.7

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.50

Bundle Diameter Max (Imperial)

0.087

Bundle Diameter Max (Metric)

2.20

Thickness T (Metric)

35.0

Width of Liner (Metric)

215.9

Width of Liner (imperial)

8.5

Outside Diameter Max(Imperial)

0.087

Outside Diameter Min (metric)

1.5

Outside Diameter Min(Imperial)

0.059

Outside Diameter Max (metric)

2.20

Material	Type 994, Polyethylene Terephthalate (PET)
Material Shortcut	994
Adhesive	Acrylic
Halogen free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature (Metric)	-40°F to +302°F (-40°C to +150°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3919905060
Labels per Column	8
Labels per Row	16
Weight (Metric)	0.521
Weight (Imperial)	1.14

