

Specification Sheet

Part Number: TAG24-100



Dot Matrix Label, Self-Laminating, 2.0" x .50" x 1.437", 4 Across, White, 5000/pkg

Article Number

595-24100

Type

TAG24

Color

White (WH)

Features & Benefits

- Dot matrix printable self-laminating vinyl has a smooth surface, allowing for the highest resolution and print contrast using an impact printer.
- The material is a conformable vinyl, allowing it to wrap and stay around wires and cable.
- The acrylic-based adhesive bonds to a wide variety of substrates and will remain in place long term.
- Tabtag dot matrix labels are specifically made for use in dot matrix printers for fast and easy printing.
- Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.

Quantity Per

pack

Product Description

HellermannTyton's self-laminating labels are used for marking wires and cable. The clear tail overlaps and protects the printed information from abrasion, chemicals and solvents and resists UV exposure. When printed using using any standard dot matrix printer, clear marking and high high-contrast imaging against the wire make this the perfect choice for durable identification.

Short Description

Dot Matrix Label, Self-Laminating, 2.0" x .50" x 1.437", 4 Across, White, 5000/pkg

Global Part Name

TAG24-100-WH

Fixation Method

Pasting / Stick

Variant

Adhesive label

Width W (Imperial)

2.0

Width W (Metric)

50.8

Bundle Diameter Min (Imperial)

0.15

Bundle Diameter Min (Metric)

3.80

Bundle Diameter Max (Imperial)

.29

Bundle Diameter Max (Metric)

7.60

Thickness T (Metric)

75.0

Width of Liner (Metric)

228.60

Width of Liner (imperial)

8.9

Outside Diameter Max(Imperial)

0.29

Outside Diameter Min (metric)

3.8

Outside Diameter Min(Imperial)

0.14

Outside Diameter Max (metric)

7.60

Material

Type 100, Vinyl (PVC), white (WH), self-laminating

Material Shortcut

100

Adhesive

Acrylic

Halogen free

No

Adhesive Operating Temperature

-51°F to +200°F (-46°C to +93°C)

Operating Temperature (Metric)

-51°F to +200°F (-46°C to +93°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Certification/Specification WEB

UL-Recognized

UL Recognized (US)

Yes

Package Quantity(Imperial)

5000

Package Quantity (Metric)

5000

| | |
|--------------------------|------------|
| Customs Number | 3919905060 |
| Labels per Column | 4 |
| Labels per Row | 4 |
| Weight (Metric) | 0.46 |
| Weight (Imperial) | 1.01 |