

## Specification Sheet

Part Number: TAG10T2-100B



Thermal Transfer Labels, Self-Laminating, 2.0" x .75" x 2.25", 2 Across, VL, White, 2500/roll

**Article Number**

596-00002

**Type**

TAG10T2

**Color**

White (WH)

**Features & Benefits**

- HellermannTyton Self-Laminating Labels come on rolls on a standard 3" core for easy loading into a printer or caddy.
- Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time.
- Labels are UL recognized for indoor and outdoor use to expand application options.
- HellermannTyton thermal transfer labels work in any thermal transfer printer so that the user always has options to get labels printed without being locked into a single vendor.

**Quantity Per**

roll

**Product Description**

HellermannTyton thermal transfer self-laminating labels are a conformable vinyl film with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels are UL recognized for indoor and outdoor use with an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.

**Short Description**

Thermal Transfer Labels, Self-Laminating, 2.0" x .75" x 2.25", 2 Across, VL, White, 2500/roll

**Global Part Name**

TAG10T2-100B-WH

**Length L (Imperial)**

2.0

**Length L (Metric)**

50.8

**Width W (Imperial)**

2.0

**Width W (Metric)**

50.8

**Bundle Diameter Min (Imperial)**

0.216

**Bundle Diameter Min (Metric)**

5.5

**Bundle Diameter Max (Imperial)**

0.476

**Bundle Diameter Max (Metric)**

12.1

**Thickness T (Metric)**

25

**Width of Liner (Metric)**

98.42

**Width of Liner (imperial)**

3.875

<b>Material</b>	Type 100B
<b>Material Shortcut</b>	100B
<b>Adhesive</b>	Acrylic
<b>Halogen free</b>	No
<b>Adhesive Operating Temperature</b>	-51°F to +200°F (-46°C to +93°C)
<b>Operating Temperature (Metric)</b>	-40°F to +194°F (-40°C to +90°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL-Recognized
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	2500
<b>Package Quantity (Metric)</b>	2500
<b>Customs Number</b>	3919102055
<b>Labels per Column</b>	1
<b>Labels per Row</b>	2
<b>Weight (Metric)</b>	1.176

**Weight (Imperial)**

2.57