


## Specification Sheet

Part Number: 596-00258



Solar Label, WARNING ELECTRICAL SHOCK HAZARD, 4.125" x 2.0", VL, Red, 50/roll

Article Number	596-00258
Type	WDCCU
Color	Red (RD)
Features & Benefits	<ul style="list-style-type: none"><li>•Pre-Printed Vinyl Solar Labels are made with UV-stable inks and materials for durability and weather resistance.</li><li>•Supplied with an aggressive adhesive to ensure long life.</li><li>•Meets NEC &amp; IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.</li><li>•Pre-printed labels offer significant time and cost savings over high priced plastic engraved phenolic placards and lead time purchased markers.</li></ul>
Quantity Per	roll

**Product Description**

HellermannTyton pre-printed vinyl Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

**Short Description**

Solar Label, WARNING ELECTRICAL SHOCK HAZARD, 4.125" x 2.0", VL, Red, 50/roll

**Global Part Name**

WDCCU-443/552-RD

**Technical Description**

Pre-Printed Solar Label, "WARNING - DC CONDUCTORS MAY BE...", 4.12" X 2", Red

**Width W (Imperial)**

4.125

**Width W (Metric)**

104.6

**Thickness T (Metric)**

64.0

**Height H (Imperial)**

2.0

**Height H (Metric)**

50.80

**Material**

Type 443/552, UV Stable Flexible White Vinyl with Acrylic Laminate

**Material Shortcut**

443/552

**Adhesive**

Acrylic

**Halogen free** No

**Adhesive Operating Temperature** -40°F to +174°F (-40°C to +79°C)

**Operating Temperature (Metric)** -40°F to +174°F (-40°C to +79°C)

**Reach Complaint(Article 33)** Yes

**ROHS Complaint** Yes

**Certification/Specification WEB** UL 969

**Warranty (US)** Yes

**UL Recognized (US)** Yes

**Package Quantity(Imperial)** 50

**Package Quantity (Metric)** 50

**Customs Number** 3919102055

**Labels per Column** 1

**Labels per Row** 1

**Weight (Metric)** 0.521

**Weight (Imperial)** 31.97

