

## Specification Sheet

Part Number: 596-00624



Terminal Block Labels, .275" wide, PE, White, 100 ft/roll

**Article Number**

596-00624

**Type**

TBL275

**Color**

White (WH)

**Features & Benefits**

- Label stock for use with thermal transfer printers.
- Strong acrylic adhesive for industrial applications.
- Abrasion and chemical resistant top coat for long lasting results.
- For use with HellermannTyton thermal transfer printers or most standard brands.

**Quantity Per**

roll

**Product Description**

To suit different industrial applications, HellermannTyton offers a wide variety of thermal transfer label stocks including polyester, metalized polyester, clear polyester, cloth, polyimide and Durattach high density polyolefin. Thermal transfer labels include a strong acrylic adhesive and abrasion and chemical resistant top coatings for long lasting results. Easily print custom labels and variable information with HellermannTyton TagPrint® Pro labeling software and a thermal transfer printer.

|                                       |                                                           |
|---------------------------------------|-----------------------------------------------------------|
| <b>Short Description</b>              | Terminal Block Labels, .275" wide, PE, White, 100 ft/roll |
| <b>Global Part Name</b>               | TBL275-PE-WH                                              |
| <b>Technical Description</b>          | Terminal Block Label, .275" wide, PE, White               |
| <b>Length L (Imperial)</b>            | 100.0                                                     |
| <b>Length L (Metric)</b>              | 30.48                                                     |
| <b>Width W (Imperial)</b>             | 0.275                                                     |
| <b>Width W (Metric)</b>               | 6.98                                                      |
| <b>Thickness T (Metric)</b>           | 64.0                                                      |
| <b>Material</b>                       | Polyethylene (PE)                                         |
| <b>Material Shortcut</b>              | PE                                                        |
| <b>Adhesive</b>                       | Rubber                                                    |
| <b>Halogen free</b>                   | No                                                        |
| <b>Adhesive Operating Temperature</b> | -40°F to +300°F (-40°C to +149°C)                         |
| <b>Operating Temperature (Metric)</b> | -40°F to +300°F (-40°C to +149°C)                         |
| <b>Reach Complaint(Article 33)</b>    | Yes                                                       |

|                                   |            |
|-----------------------------------|------------|
| <b>ROHS Complaint</b>             | Yes        |
| <b>UL Recognized (US)</b>         | Yes        |
| <b>Package Quantity(Imperial)</b> | 100        |
| <b>Package Quantity (Metric)</b>  | 30.48      |
| <b>Customs Number</b>             | 3919102055 |
| <b>Labels per Column</b>          | 1          |
| <b>Labels per Row</b>             | 1          |
| <b>Weight (Metric)</b>            | 0.68       |
| <b>Weight (Imperial)</b>          | 1.48       |