

Specification Sheet

Part Number: 596-00669



Solar Label, 2017 Code, 120 VOLT SUPPLY..., 3.75" x 2.0", VL, Orange, 10/pkg

Article Number	596-00669
Type	120VOLT10
Color	Orange (OG)
Features & Benefits	<ul style="list-style-type: none">•Pre-Printed Vinyl Solar Labels are made with UV-stable inks and materials for durability and weather resistance.•Supplied with an aggressive adhesive to ensure long life.•Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.•Pre-printed labels offer significant time and cost savings over high priced plastic engraved phenolic placards and lead time purchased markers.
Quantity Per	pack

Product Description

HellermannTyton pre-printed vinyl Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description

Solar Label, 2017 Code, 120 VOLT SUPPLY..., 3.75" x 2.0", VL, Orange, 10/pkg

Global Part Name

120VOLT10-443/552-OG

Technical Description

Solar Label, Warning - 120-Volt Supply Solar Label, 3.75" X 2.0", Orange/White

Local Order Number 2

Cross Reference = 50 per roll: 596-00591; Metal Solar Placard 5 pack: 596-00837; Spanish version 50 per roll: 596-00824

Width W (Imperial)

3.75

Width W (Metric)

92.25

Height H (Imperial)

2.0

Height H (Metric)

50.80

Material

Type 443/552, UV Stable Flexible White Vinyl with Acrylic Laminate

Material Shortcut

443/552

Adhesive

Acrylic

Halogen free No

Adhesive Operating Temperature -40°F to +174°F (-40°C to +79°C)

Operating Temperature (Metric) -40°F to +174°F (-40°C to +79°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB NEC2017 UL 969

Warranty (US) Yes

UL Recognized (US) Yes

Package Quantity(Imperial) 10

Package Quantity (Metric) 10

Customs Number 3919102055

Labels per Column 1

Labels per Row 1

Weight (Metric) .104

Weight (Imperial) 0.23

