

Specification Sheet

Part Number: 596-00746

DC COMBINER BOX

Solar Label, DC COMBINER BOX, 4.0" x 1.0", VL, Red, 10/pkg

Article Number

596-00746

Type

DCCB10

Color

Red (RD)

Features & Benefits

- Pre-Printed Vinyl Solar Labels are made with UV-stable inks and materials for durability and weather resistance.
- Supplied with an aggressive adhesive to ensure long life.
- Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.
- Pre-printed labels offer significant time and cost savings over high priced plastic engraved phenolic placards and lead time purchased markers.

Quantity Per

pack

Product Description

HellermannTyton pre-printed vinyl Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description

Solar Label, DC COMBINER BOX, 4.0" x 1.0", VL, Red, 10/pkg

Global Part Name

DCCB10-443/552-RD

Technical Description

Pre-Printed Solar Label, 4" X 1", DC Combiner Box, Vinyl, Red, 10/PK

Width W (Imperial)

4.0

Width W (Metric)

101.6

Height H (Imperial)

1.0

Height H (Metric)

25.40

Material

Type 443/552, UV Stable Flexible White Vinyl with Acrylic Laminate

Material Shortcut

443/552

Adhesive

Acrylic

Halogen free

No

Adhesive Operating Temperature

-40°F to +174°F (-40°C to +79°C)

Operating Temperature (Metric) -40°F to +174°F (-40°C to +79°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB NEC2014

Warranty (US) Yes

UL Recognized (US) Yes

Package Quantity(Imperial) 10

Package Quantity (Metric) 10

Customs Number 3919905060

Labels per Column 1

Labels per Row 1

Weight (Metric) .104

Weight (Imperial) 0.23