

Specification Sheet

Part Number: 596-00852



Article Number	596-00852
Type	PVACDIS10
Color	Red (RD)
Features & Benefits	<ul style="list-style-type: none">• Made with UV-stable inks and materials for durability and weather resistance.• Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.• High abrasion and scuff resistance for high-performance labeling.• Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.
Quantity Per	pack

Product Description

HellermannTyton pre-printed Solar Rating labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description	Solar Label, Printable, PHOTOVOLTAIC AC DISCONNECT, 3.75" x 1.0", PET, Red, 10/pkg
Global Part Name	PVACDIS10-840/926-RD
Technical Description	Printable Solar Label, PV AC RATING LABEL, 3.75" X 1.0", Red
Local Order Number 2	Cross Reference = 50 per roll: 596-00239; Printable Metal Solar Placard 5 pack: 596-00838; Engravable Metal Solar Placard 5 pack: 596-00859; Spanish version 50 per roll: 596-00818
Length L (Imperial)	1.0
Length L (Metric)	25.4
Width W (Imperial)	3.75
Width W (Metric)	95.25
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Type 840/926, Polyester (PET), UV stable, clear Polyester laminate
Material Shortcut	840/926
Adhesive	Acrylic

Halogen free No

Adhesive Operating Temperature -40°F to +302°F (-40°C to +150°C)

Operating Temperature (Metric) -40°F to +302°F (-40°C to +150°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB NEC2014 CSA 66956

Warranty (US) Yes

UL Recognized (US) Yes

Package Quantity(Imperial) 10

Package Quantity (Metric) 10

Customs Number 3919905060

Labels per Column 1

Labels per Row 1

Weight (Metric) 0.521

Weight (Imperial) 1.14

