

Specification Sheet

Part Number: 596-00868



Metal Solar Placard, Blank Plate For Engraving, 3.75" x 2.0", AL, Orange/Black, 5/pkg

Article Number	596-00868
Type	BLANK375X2
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.• Aggressive adhesive ensures strong bond, even on powder coated surfaces.• Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.• Optional Paint Shields provide additional protection for pre-printed and variable data placards.
Quantity Per	pack

Product Description

Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, HellermannTyton offers two styles of variable placards: hand-writable and engravable. Both hand-writable placards feature a silver variable data area that can be marked using an industrial paint pen. Engravable placards have a black area that can be engraved using standard engraving equipment.

Short Description

Metal Solar Placard, Blank Plate For Engraving, 3.75" x 2.0", AL, Orange/Black, 5/pkg

Global Part Name

BLANK375X2-AA-BK

Technical Description

3.75" X 2.00" Black text on an Orange/black sign for engraving custom metal placards - 5 per pack.

Length L (Imperial)

3.75

Length L (Metric)

95.25

Width W (Imperial)

3.75

Width W (Metric)

95.25

Height H (Imperial)

2.0

Height H (Metric)

50.80

Material

Anodized Aluminum (AA)

Material Shortcut

AA

Adhesive

Ultra High Bond Permanent Acrylic Adhesive

Halogen free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature (Metric)	-40°F to +203°F (-40°C to +95°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	NEC2014 NEC2017
Warranty (US)	Yes
Package Quantity(Imperial)	5
Package Quantity (Metric)	5
Customs Number	3919905060
Labels per Column	1
Labels per Row	1
Weight (Metric)	.104
Weight (Imperial)	0.23

