


Specification Sheet

Part Number: 596-00886



Solar Label, Reflective, 2017 Code, SOLAR PV SYSTEM...SHUTDOWN, 6.0" x 4.0", VL, Red, 50/pkg

| | |
|---------------------|---|
| Article Number | 596-00886 |
| Type | RSDRD17 |
| Color | Red (RD) |
| Features & Benefits | <ul style="list-style-type: none">•Made with UV-stable inks and materials for durability and weather resistance.•Reflective properties to meet applicable NEC code requirements for reflective identification.•Supplied with an aggressive adhesive to ensure long life.•Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections. |
| Quantity Per | pack |

Product Description

HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code (NEC) and the International Fire Code (IFC) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description

Solar Label, Reflective, 2017 Code, SOLAR PV SYSTEM...SHUTDOWN, 6.0" x 4.0", VL, Red, 50/pkg

Global Part Name

RSDRD17-242/552-RD

Technical Description

Pre-Printed Solar Label, Reflective-2017 Code, Rapid Shutdown Label - Roof Hazard, 6.0" X 4.0", Vinyl, Yellow, 50/RL

Length L (Metric)

101.6

Width W (Imperial)

6.0

Width W (Metric)

152.4

Thickness T (Metric)

64.0

Height H (Imperial)

4.0

Height H (Metric)

101.60

Material

Type 242/552, UV Stable Reflective Vinyl w/Acrylic Laminate

Material Shortcut

242/552

| | |
|--|-----------------------------------|
| Adhesive | Acrylic |
| Halogen free | No |
| Adhesive Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
| Operating Temperature (Metric) | -40°F to +174°F (-40°C to +79°C) |
| Reach Complaint(Article 33) | Yes |
| ROHS Complaint | Yes |
| Certification/Specification WEB | NEC2017 |
| Warranty (US) | Yes |
| UL Recognized (US) | Yes |
| Package Quantity(Imperial) | 50 |
| Package Quantity (Metric) | 50 |
| Customs Number | 3919102055 |
| Labels per Column | 1 |
| Labels per Row | 1 |
| Weight (Metric) | .104 |
| Weight (Imperial) | 0.23 |

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)