

Specification Sheet

Part Number: 596-00919



Article Number

596-00919

Type

PVACDIS17M5

Color

Black (BK)

Features & Benefits

- Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.
- Aggressive adhesive ensures strong bond, even on powder coated surfaces.
- Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.
- Optional Paint Shields provide additional protection for pre-printed and variable data placards.

Quantity Per

pack

Product Description

Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, HellermannTyton offers two styles of variable placards: hand-writable and engravable. Both hand-writable placards feature a silver variable data area that can be marked using an industrial paint pen. Engravable placards have a black area that can be engraved using standard engraving equipment.

Short Description	Metal Solar Placard, Hand Writable, 2017 Code, PV AC DISCONNECT..., 3.75" x 1.0", AL, Black, 5/pkg
Global Part Name	PVACDIS17M5-AA-BK
Technical Description	3.75" X 1" Silver aluminum text on black background that reads as: "PHOTOVOLTAIC AC DISCONNECT. RATED AC OUTPUT CURRENT. NOMINAL OPERATING AC VOLTAGE." 5 per pack. Nameplate is also printable using a paint pen to add the variable voltage information on demand.
Length L (Imperial)	1.0
Length L (Metric)	25.4
Width W (Imperial)	3.75
Width W (Metric)	95.25
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive
Halogen free	No

Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature (Metric)	-40°F to +203°F (-40°C to +95°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	NEC2017
Warranty (US)	Yes
Package Quantity(Imperial)	5
Package Quantity (Metric)	5
Customs Number	3919102055
Labels per Column	1
Labels per Row	1
Weight (Metric)	.104
Weight (Imperial)	0.23