

Specification Sheet

Part Number: 596-00927



Article Number

596-00927

Type

VM120C

Color

Orange (OG)

Features & Benefits

- HellermannTyton Voltage Markers are available in three sizes to best suit application requirements.
- Glare-free surface for easy identification from any angle.
- Resists moisture for long-lasting durability.
- Markers are flexible to wrap securely around various size wires, pipes and conduit.

Quantity Per

pack

Product Description

HellermannTyton Pre-Printed Voltage Markers are made of durable vinyl and are available with the most commonly used warnings and alerts. The self-adhesive markers allow users to clearly identify electrical lines, voltages and hazards. The durable adhesive backing is resistant to UV exposure as well as chemicals and solvents. Use voltage markers on conduit, pipe, circuit boxes or electrical panels.

Short Description	Voltage Marker, .50" x 2.25", 120 Volts, Vinyl, Orange, 17/card, 50 cards/pkg
Global Part Name	VM120C-V-OG
Technical Description	Voltage Marker, 120 Volts, .50" x 2.25", 18 Per Card, 50/pkg
Length L (Imperial)	2.25
Length L (Metric)	57.15
Width W (Imperial)	2.25
Width W (Metric)	57.15
Thickness T (Imperial)	4
Thickness T (Metric)	.10
Height H (Imperial)	0.50
Height H (Metric)	12.70
Material	Vinyl
Material Shortcut	V
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)

Operating Temperature (Metric)

-40°F to +176°F (-40°C to +80°C)

ROHS Complaint

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3919905060

Weight (Metric)

0.45

Weight (Imperial)

0.5