

## Specification Sheet

Part Number: TAG72T1-795



Thermal Transfer Labels, 2.75" x 1.25", 1 Across, Polyester, Silver, 3000/roll

**Article Number**

596-72795

**Type**

TAG72T1

**Color**

Silver (SR)

**Features & Benefits**

- Thermal transfer labels are made with high performance materials for long term industrial applications.
- Labels can be printed in any standard thermal transfer printer giving the user options for printing and eliminating the need to be dedicated to one printer model.
- The labels are available in a wide variety of sizes so that finding a label for a particular application is easy.

**Quantity Per**

roll

**Product Description**

Labels are made with various high performance materials including polyester, metalized polyester, clear polyester, cloth, polyimide and the Durattach label stock. The construction includes an aggressive acrylic adhesive and abrasion and chemical resistant top coatings that are made to accept ink from a thermal transfer printer. The product is supplied on rolls on a 3" cardboard core.

<b>Short Description</b>	Thermal Transfer Labels, 2.75" x 1.25", 1 Across, Polyester, Silver, 3000/roll
<b>Global Part Name</b>	TAG72T1-795-ML
<b>Length L (Imperial)</b>	2.75
<b>Length L (Metric)</b>	69.85
<b>Width W (Imperial)</b>	2.75
<b>Width W (Metric)</b>	69.85
<b>Thickness T (Metric)</b>	64.0
<b>Height H (Imperial)</b>	1.25
<b>Height H (Metric)</b>	30.98
<b>Width of Liner (Metric)</b>	74.95
<b>Width of Liner (imperial)</b>	2.95
<b>Material</b>	Type 795, Polyester (PET)
<b>Material Shortcut</b>	795
<b>Adhesive</b>	Acrylic
<b>Halogen free</b>	No

<b>Adhesive Operating Temperature</b>	-100°F to +352°F (-73°C to +178°C)
<b>Operating Temperature (Metric)</b>	-40°F to +300°F (-40°C to +149°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL-Recognized
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	3000
<b>Package Quantity (Metric)</b>	3000
<b>Customs Number</b>	3919102055
<b>Labels per Column</b>	1
<b>Labels per Row</b>	1
<b>Weight (Metric)</b>	0.68
<b>Weight (Imperial)</b>	1.48

