

## Specification Sheet

Part Number: 596-96253



Paint Mask Label, 1.0" X .75" X 4.75", 1 Across, Vinyl, White, 1000/roll

<b>Article Number</b>	596-96253
<b>Type</b>	PW.25W1
<b>Color</b>	White (WH)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Paint Mask Labels provide permanent paint protection but can still be removed at any time when required.</li><li>• Paint Mask Labels withstand chemicals and heat to survive the painting process.</li></ul>
<b>Quantity Per</b>	roll
<b>Product Description</b>	HellermannTyton thermal transfer self-laminating Paint Mask Labels are conformable with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels utilize an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.
<b>Short Description</b>	Paint Mask Label, 1.0" X .75" X 4.75", 1 Across, Vinyl, White, 1000/roll

**Global Part Name**

PW.25W1-V-WH

**Technical Description**

Paint Mask Label, 1.0" X .75" X 4.75", 1 across, 1 piece design, .25" cable diameter, Vinyl, White, 1000/RL

**Width W (Imperial)**

1.0

**Width W (Metric)**

25.4

**Bundle Diameter Min (Imperial)**

.125

**Bundle Diameter Min (Metric)**

3.17

**Bundle Diameter Max (Imperial)**

.375

**Bundle Diameter Max (Metric)**

9.52

**Thickness T (Metric)**

64.0

**Height H (Imperial)**

0.75

**Height H (Metric)**

19.0

**Width of Liner (Metric)**

50.8

**Width of Liner (imperial)**

2.0

**Material**

Vinyl

**Material Shortcut**

V

<b>Adhesive</b>	Acrylic
<b>Halogen free</b>	No
<b>Adhesive Operating Temperature</b>	-51°F to +200°F (-46°C to +93°C)
<b>Operating Temperature (Metric)</b>	-40°F to +194°F (-40°C to +90°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL-Recognized
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3919102055
<b>Labels per Column</b>	1
<b>Labels per Row</b>	1
<b>Weight (Metric)</b>	0.68
<b>Weight (Imperial)</b>	1.48

