

## Specification Sheet

Part Number: 596-96255



Paint Mask Label, 1.0" x 0.75" x 4.75", 1 Across, Polyester, White, 1000/roll

<b>Article Number</b>	596-96255
<b>Type</b>	PW.25W1P
<b>Color</b>	White (WH)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Paint Mask Labels provide permanent paint protection but can still be removed at any time when required.</li><li>• Paint Mask Labels withstand chemicals and heat to survive the painting process.</li></ul>
<b>Quantity Per</b>	roll
<b>Product Description</b>	HellermannTyton thermal transfer self-laminating Paint Mask Labels are conformable with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels utilize an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.
<b>Short Description</b>	Paint Mask Label, 1.0" x 0.75" x 4.75", 1 Across, Polyester, White, 1000/roll

**Global Part Name**

PW.25W1P-PET-WH

**Technical Description**

Paint Mask Label, 1.0" X .75" X 4.75", 1 across, 1 piece design, .25" cable diameter, Polyester, White, 1000/RL

**Width W (Imperial)**

1.0

**Width W (Metric)**

25.4

**Bundle Diameter Min (Imperial)**

.125

**Bundle Diameter Min (Metric)**

3.17

**Bundle Diameter Max (Imperial)**

.375

**Bundle Diameter Max (Metric)**

9.52

**Thickness T (Metric)**

64.0

**Height H (Imperial)**

0.75

**Height H (Metric)**

19.0

**Width of Liner (Metric)**

50.8

**Width of Liner (imperial)**

2.0

**Material**

Polyester Film

**Material Shortcut**

PET

**Adhesive**

Acrylic

MIL-STD-810G

**US MIL SPEC**

MIL-STD-202

**Halogen free**

No

**Adhesive Operating Temperature**

-40°F to +302°F (-40°C to +150°C)

**Operating Temperature (Metric)**

-40°F to +300°F (-40°C to +149°C)

**Reach Complaint(Article 33)**

Yes

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

1000

**Package Quantity (Metric)**

1000

**Customs Number**

3919102055

**Labels per Column**

1

**Labels per Row**

1

**Weight (Metric)**

0.68

**Weight (Imperial)**

1.48

