

Specification Sheet

Part Number: FOM-75



Fiber Optic Cable Marker, 1.5" x .75", Polyethylene, Orange, 25/pkg

Article Number	597-00039
Type	FOM
Color	Orange (OG)
Features & Benefits	<ul style="list-style-type: none">• Manufactured from thick .05" polyethylene for long term durability.• Mounting holes for easy mounting using standard cable ties.• Markers can be mounted in any direction, either vertically, horizontally, as a wrap-around identification plate or as a flag for the best visual position on the cable assembly.
Quantity Per	pack
Product Description	HellermannTyton's cable markers are made from .05" thick polyethylene and can be marked using a permanent felt tip marker.
Short Description	Fiber Optic Cable Marker, 1.5" x .75", Polyethylene, Orange, 25/pkg
Global Part Name	FOM-PE-OG

Length L (Imperial)	1.5
Length L (Metric)	19.05
Width W (Imperial)	1.5
Width W (Metric)	38.1
Height H (Imperial)	0.75
Height H (Metric)	19.05
Material	Polyethylene (PE)
Material Shortcut	PE
Adhesive	Acrylic
Halogen free	No
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature (Metric)	-150°F to +149°F (-101°C to +65°C)
Reach Complaint(Article 33)	No
ROHS Complaint	Yes

Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988
Weight (Metric)	0.453
Weight (Imperial)	.2