

Specification Sheet

Part Number: 597-00099



Caution Sign, 10" x 14", Do Not Operate Without Guards, Vinyl, Yellow, 25/pkg

Article Number	597-00099
Type	CS1014DNOWG
Color	Yellow (YE)
Features & Benefits	<ul style="list-style-type: none">• HellermannTyton Signs meet the demanding needs of today's applications, providing dependable identification.• Signs are code and ANSI compliant to meet all municipal requirements.
Quantity Per	pack
Product Description	HellermannTyton Pre-Printed Safety Signs are made of durable vinyl and are supplied with the most commonly used warnings and alerts. The signs are designed to be mounted using an aggressive acrylic adhesive.
Short Description	Caution Sign, 10" x 14", Do Not Operate Without Guards, Vinyl, Yellow, 25/pkg

Global Part Name

CS1014DNOWG-V-YE

Technical Description

CAUTION Do Not Operate Without Guards, 10" x 14", 25/pkg

Length L (Imperial)

14.0

Length L (Metric)

355.60

Width W (Imperial)

14

Width W (Metric)

355.6

Thickness T (Imperial)

4

Thickness T (Metric)

.10

Height H (Imperial)

10.0

Height H (Metric)

254.0

Material

Vinyl

Material Shortcut

V

Adhesive

Acrylic

Halogen free

No

UV Resistant (Yes/No)

No

Adhesive Operating Temperature -40°F to +176°F (-40°C to +80°C)

Operating Temperature (Metric) -90°F to +186°F (-67°C to +75°C)

ROHS Complaint Yes

Package Quantity(Imperial) 25

Package Quantity (Metric) 25

Customs Number 3919905060

Weight (Metric) 0.45

Weight (Imperial) 0.5