


Specification Sheet

Part Number: TYHC14



Article Number

598-00036

Type

TYHC14

Color

White (WH)

Features & Benefits

- Handi-Cards have a split backing so that a portion of the liner can be removed to expose the markers for easy dispensing.
- Handi-Cards are kitted on the card so that specific markers can be removed without affecting the other markers on the card.
- Markers are pre-printed so no additional post printing is required, saving time and money.
- Label material is a conformable cloth that ensures markers stay on wires and cables for the life of the application.

Quantity Per

pack

Product Description

HellermannTyton Handi-Cards are easy release pre-printed cloth markers, on a plastic card, with a strong adhesive for a long lasting bond on wire and cable. The markers are available in Solid format where each marker on the card contains the same legend and Sequence format where each marker on the card contains a different number or letter which is usually printed in sequence from lowest to highest in sort order.

Short Description

Handi-Card Wire and Cable Markers, .25" x 1.5", Solid #14, 36 Per Card, TYHC, White, 25/pkg

Global Part Name

TYHC14-TYHC-WH

Length L (Imperial)

1.5

Length L (Metric)

38.1

Width W (Imperial)

0.25

Width W (Metric)

6.35

Bundle Diameter Min (Imperial)

.13

Bundle Diameter Min (Metric)

3.40

Bundle Diameter Max (Imperial)

.29

Bundle Diameter Max (Metric)

7.50

Height H (Imperial)

1.50

Height H (Metric)

38.10

Outside Diameter Max(Imperial)

.290

Outside Diameter Min (metric)

3.40

Outside Diameter Min(Imperial)

.130

Outside Diameter Max (metric)

7.50

Material	Vinyl Cloth (TYHC)
Material Shortcut	TYHC
Adhesive	Rubber
Adhesive Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Operating Temperature (Metric)	-40°F to +248°F (-40°C to +120°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	5903103000
Labels per Column	1
Labels per Row	36